

# DuraLaser Fluorescent Colors Instructions

DuraLaser colors are the brightest and boldest DuraCoat colors yet while offering the same durability and corrosion free properties as the original DuraCoat finishes. DuraLaser can be applied to all types of metal, plastic, and wood including optics and accessories.

- 1) Disassemble firearm as far as you feel comfortable.
- 2) Degrease parts with LCW TruStrip Cleaner/Degreaser.
- 3) If coating over an existing paint, spray on, or bake on finish, or if you do not know what the existing finish is, we recommend roughing up the surface by sanding or sandblasting.
- 4) Apply a base coat of DuraCoat White
- 5) Allow the DuraCoat base coat to dry for at least one hour.
- 6) Mix 8 parts DuraLaser with 1 part hardener.
- 7) Reduce with DuraLaser Reducer only if necessary up to 20% by volume
- 8) Apply DuraLaser with an airbrush or spray gun. Allow to dry at least 20 minutes.
- 9) Top coat with DuraLaser Clear. Allow to dry.
- 10) Do not allow more than 7 days to pass between the base coat and top coat.

Parts coated with DuraLaser can be reassembled and used after 24 hours. It will take 3-4 weeks for a full cure to be reached. Do not apply harsh cleaners, use in holster, or subject to harsh use during the cure time.